Easyclose 100kg


FITTING INSTRUCTIONS - NOTICE DE POSE - MONTAGE HANDLEIDING - MONTAGEANLEITUNG ISTRUZIONI DI MONTAGGIO - INSTUCCIONES DE MONTAJE


The Easyclose door closer uses pneumatic technology to automatically keep your door closed. The standard length of retracted closer body is 28"/70cm, with maximum travelling of 50"/125cm, suitable for most width doors.




IMPORTANT information before installation

- The closing performance of Easyclose is affected mainly by the door's rolling efficiency.
- If the rolling efficiency is not smooth enough the Easyclose may not show its best closing performance.
- A top rolling system on doors is smoother than floor track doors, enhancing the Easyclose performance.









2. Fit the Flex bracket base plate

Mount the Flex bracket base plate with the 3 small screws **B** supplied.




3. Fit the Flex bracket




4. Regulate the closing speed

The closing speed can be regulated by turning the adjusting screw clockwise for slower and anticlockwise for faster.




Check the opening and closing operation for obstructions which could effect the units performance.


5. Fitting the optional fascia





APPENDIX A - Husky Track Suggested Fitting Methods

FASCIA NOT SUPPLIED BY PCH - FASCIA TO OVERLAP DOOR BY 5mm FASCIA TO BE AT LEAST 10 mm THICK - CONSULT TABLES FOR VALUES













Soltaire Track Suggested Fitting Methods

FASCIA NOT SUPPLIED BY PCH - FASCIA TO OVERLAP DOOR BY $5\,\mathrm{mm}$ FASCIA TO BE AT LEAST 10 mm THICK - CONSULT TABLE FOR VALUE F









Marathon Track Suggested Fitting Methods

FASCIA NOT SUPPLIED BY PCH - FASCIA TO OVERLAP DOOR BY 5mm - FASCIA TO BE AT LEAST 10 mm THICK

